

PROJECTINA

DOCUSTAT

DS-220

**VISUALISE INDENTED WRITING
ON DOCUMENTS WITH OUR
DOCUSTAT DS-220**



projectina®



RESPONDS ONLY TO INDENTED WRITING - IGNORES VISIBLE SCRIPT

TILTING AND COLLECTION DEVICE FOR EASY EMPTYING OF TONER



PREPARATION WITH DOCUMENT HUMIDIFIER TO INCREASE SENSITIVITY OF DOCUMENTS

TIMER FOR CORONA EXPOSURE AND PRE-SET OF VOLTAGE FOR CORONA



VENTILATION FOR AIRBORNE TONER PARTICLES

THE SUPPLIED PLASTIC FILM, TYPE IW, IS USED FOR SECURING OF INDENTED WRITING

PRODUCES PERMANENT 1 TO 1 TRANSPARENCIES



LEAVES DOCUMENTS UNCONTAMINATED


FOR SMALL AND LARGE SHEETS

MORE SENSITIVE THAN OBLIQUE LIGHTING

Weight Basic System: approx. 21 kg
Mains connection: 100-240V/50Hz-60Hz
Vacuum pump: -800 mbar
High voltage power supply: 2.5 W

REVEAL THE HIDDEN DETAILS - SEE INDENTED WRITING LIKE NEVER BEFORE





DOCUMENT HUMIDIFIER
OPTION: 118258-K-9



TONER PAD OPTION:
112160-4-9

Recommended consumables:

- Cascade developer, 1 kg
- Toner
- Plastic film for indented writing, type IW, 1 roll, size 0,4 x 500 m
- Adhesive film, pack with 24 sheets each, size 25 x 35 cm (A4)
- Adhesive film, pack with 24 sheets each, size 50 x 35 cm (A3)
- Collecting tub



COLLECTING TUB OPTION: 119464-4-2

Technical Specification Basic System

- Basic unit: 450 x 440 x 210 mm with cascade developer and integrated ON/OFF fan including filter to prevent powder scattering, ON/OFF pump, with connection to corona unit
- Vacuum plate: 424 x 424 mm (A3 - replaceable)
- Suction surface in the vacuum plate
- Corona unit ON/OFF
- Plastic film for indented writing, type IW, 1 roll, size 0,4 x 500 m (including cutter)
- Adhesive film, 2 Packs with 24 sheets each, size 25 x 35 cm
- Cascade developer, 1 kg
- Toner with spoon, 1 kg
- Empty can for toner/cascade mixture
- Breathing mask
- Mains connection cable

