

PROJECTINA

DOCUSTAT
DS-220

VISUALISE INDENTED WRITING ON DOCUMENTS WITH OUR DOCUSTAT DS-220



projectina®



RESPONDS ONLY
TO INDENTED
WRITING -
**IGNORES VISIBLE
SCRIPT**

TILTING AND
COLLECTION
DEVICE FOR
**EASY EMPTYING
OF TONER**



PREPARATION
WITH **DOCUMENT
HUMIDIFIER** TO
INCREASE
SENSITIVITY OF
DOCUMENTS

**TIMER FOR
CORONA
EXPOSURE AND
PRE-SET OF
VOLTAGE FOR
CORONA**



**VENTILATION
FOR AIRBORNE
TONER
PARTICLES**

THE SUPPLIED
**PLASTIC FILM,
TYPE IW**, IS USED
FOR SECURING
OF INDENTED
WRITING

PRODUCES
PERMANENT
**1 TO 1
TRANSPAR-
ENCIES**



LEAVES
DOCUMENTS
**UNCONTAM-
INATED**


FOR **SMALL AND
LARGE SHEETS**

**MORE SENSITIVE
THAN OBLIQUE
LIGHTING**

Weight Basic System: approx. 21 kg
Mains connection: 100-240V/50Hz-60Hz
Vacuum pump: -800 mbar
High voltage power supply: 2.5 W

**REVEAL THE HIDDEN
DETAILS - SEE INDENTED
WRITING LIKE NEVER
BEFORE**





DOCUMENT HUMIDIFIER
OPTION: 118258-K-9



TONER PAD OPTION:
112160-4-9

Recommended consumables:

- Cascade developer, 1 kg
- Toner
- Plastic film for indented writing, type IW, 1 roll, size 0,4 x 500 m
- Adhesive film, pack with 24 sheets each, size 25 x 35 cm (A4)
- Adhesive film, pack with 24 sheets each, size 50 x 35 cm (A3)
- Collecting tub



COLLECTING TUB OPTION: 119464-4-2

Technical Specification Basic System

- Basic unit: 450 x 440 x 210 mm with cascade developer and integrated ON/OFF fan including filter to prevent powder scattering, ON/OFF pump, with connection to corona unit
- Vacuum plate: 424 x 424 mm (A3 - replaceable)
- Suction surface in the vacuum plate
- Corona unit ON/OFF
- Plastic film for indented writing, type IW, 1 roll, size 0,4 x 500 m (including cutter)
- Adhesive film, 2 Packs with 24 sheets each, size 25 x 35 cm
- Cascade developer, 1 kg
- Toner with spoon, 1 kg
- Empty can for toner/cascade mixture
- Breathing mask
- Mains connection cable

